ACCESSORIES

SUCTION DEVICE - LEVEL PROBE - Solenoid Pumps





Technical characteristics

These are pre-assembled suction devices, made of PVC/PP, with foot valve to allow accurate operation of the metering pump. Suction devices are equipped with foot filter. Standard version in FPM; EPDM version available on request.

These are manifactured with or without level control that allows to stop the pump or to give alarm 50 mm above the lowest suction point.

				WITHOUT Level Probe	WITH Level Probe
Ø 4x6	Ø 8x12	Dimension	Tank suitability	Code	Code
•		450x22	SER 50	9900100074	9900100075
	•	450x34		9900100076	9900100077
•		650x22	SER 100	9900100085	9900100087
	•	650x34		9900100089	9900100165
•		900x22	SER 250	9900100084	9900100086
	•	900x34		9900100088	9900100090
•		1050x22	SER 300	9900100158	9900100160
	•	1050x34		9900100162	9900100166
•		1250x22	SER 500 SER 1000	9900100159	9900100161
	•	1250x34		9900100163	9900100167

Accessories for Suction Devices











Description	Dimension	Code
Level probe + bracket: Useful to avoid dry pump dosing. Supplied with bracket to be connected with TeknaEVO pump foot filter.		EM99121000
Level probe: Made of PVC. Useful to avoid dry pump dosing. Reliable and well-built, it is resistant with almost marked chemical products. Suitable for all application.	450x22	9900100073
	200x22	9900106304
Extension modules: Made of PVC. Available for all suction devices sizes.	200x34	9900106306
Useful to adapt suction devices to the chemical tank.	450x22	9900106305
	450x34	9900106307
	580 mm	0000123061
Level probe protection tube : Made of PVC. Used to protect the probe against the turbulence around the	900 mm	0000123062
level probe when a mixer is installed. 1090 mm		0000123063
Tank/cap adaptor: Used to protect the operator against the chemical product fumes because it closes hermetically the hole where suction devices is inserted.		0000190006

www.createflow.cz

ACCESSORIES

SUCTION DEVICE - LEVEL PROBE - Solenoid Pumps



REED Switch Datasheet




PICTURE



Reed Switch - Miniature - Normally Open Contacts

Part Number: GC3723 **Product Data Sheet**

DIMENSIONS



(UL) File Number E103299

✓ RoHS Compliant


Drawings not to scale All dimensions in mm (inches) nominal.

SPECIFICATION						
Contact Form		Normally Open				
Contact Material		Rhodium				
Switching Capacity	Max.	40 VA				
Switching Voltage	Max.	230 VAC/DC				
Switching Current	Max.	2.0 A				
Carrying Current	Max.	3.0 A				
Dielectric Strength	Min.	400 VDC				
Contact Resistance	Max.	80 mOhms				
Insulation Resistance	Min.	10 ¹¹				
Pull - In - Sensitivity		30 - 50 AT				
Drop - Out - Sensitivity	Min.	15				
Bounce Time	Max.	0.5 ms				
Release Time	Max.	0.10 ms				
Resonant Frequency	Тур.	4200 Hz				
Operating Frequency	Max.	300 Hz				
Vibration (10-1000Hz)		35 g				
Shock (11 ms)		50				
Capacitance	Тур.	0.5 pF				
Operating Temperature Range		-40°C + 125°C				
Test Coil	Туре	1700				

NOTE

- When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm (.118in.) to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.
- We offer a crop and form service for Reed Switches to be customized to your specification.

Ordering Information



Did you know we also sell?







Example:

Type 3723 Standard Sensitivity. Pull-in sensitivity between 30-50 AT is PART NO: 3723 30 50 Available in ranges of 5 AT e.g: 30-35, 35-40 etc.

www.createflow.cz

Rev. No.	Revision Note	Date	Signature	
2	Datasheet Redesign	26-05-06	NG	



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Fax: (1) 973 777 8405 Phone: (1) 973 777 6900 www.comus-intl.com

©2006 Copyright Comus International Ltd, 454 Allwood Road, Clifton, New Jersey, 07012, USA.